



COVIDIEN

positive results for life™

RapidVac™ Smoke Evacuator System

The RapidVac™ smoke evacuator system improves your environment, visibility* and performance — *quietly*.

MORE POWER

The RapidVac™ smoke evacuator system has 30 percent more power at maximum air flow than our previous model.

EFFECTIVE FILTER TECHNOLOGY

All-in-one, four-stage, high-technology, long-life, three-port, RFID-equipped ULPA filter provides 99.9995 percent filtration efficiency at 0.12 micron particle size.

EASY TO USE*

Easily understandable graphics, easy to set up, easily determined airflow and filter life, and easy filter replacement.

ECONOMICAL

Long filter life, 25 hours activation time. Three ports for common filter sizes. No need for prefilters or adapters, reducing cost per procedure.

QUIET*

The RapidVac™ smoke evacuator system is quieter than our previous model and judged in surveys as quieter than expected in the O.R.



RAPIDVAC™ SMOKE EVACUATOR SYSTEM

The RapidVac™ smoke evacuator teams up with the ForceTriad™ energy platform and the Force FX™ and Force EZ™ generators. Optional accessories are available to enable other generators to synchronize with RapidVac™.

RapidVac™ Smoke Evacuator Technical Specifications

Dimensions:	8 in. high x 14 in. wide x 18 ¾ in. deep
Weight:	20 lbs.
Filter:	ULPA: 99.9995% efficient at 0.12 microns Pre-filter: Rated for 0.3 micron filtration
Electrical:	Voltage operating range: 200-132 VAC, 50 Hz; current: 10 amps, maximum 200-240 VAC, 60 Hz; current: 8 amps, maximum
Compatible Carts:	FT900 Mounting cart system - main, upper, or lower shelf UC8009 Universal mounting cart UC8013 Suspended shelf for
Certifications and Markings:	UL, CE, cUL

ORDER INFORMATION

Catalog Number	Description	Order Quantity
Smoke Evacuator and Accessories		
SE3690	RapidVac™ smoke evacuator 100-132 V	1 each
SE3695	RapidVac™ smoke evacuator 200-240 V	1 each
SEA3730	RapidVac™ system interlink cable, for use with the ForceTriad™	1 each
SEA3740	RapidVac™ remote switch activator (for use with any electrosurgical generator)	1 each
SEA3745	RapidVac™ footswitch, pneumatic, with 3 m (10 ft) cord	1 each
Tubeing and Filters		
SEA3700	RapidVac™ smoke evacuator ULPA filters (2 pack)	2/case
SEA3735	AccuVac™ pencil adapter attachment, with 1 cm (3/8 in.) tubing, 3 m (10 ft), sterile	Coming soon
SEA3720	Smoke vac tubing kit w/valve, sterile	12/case
SEA3715	2.2 cm (7/8 in.) tubing (10 ft), sterile	12/case
SEA3710	1 cm (3/8 in.) tubing, 3 m (10 ft), sterile	10/case
SEA3725	Laser-resistant wand, 2.2 cm (7/8 in.), sterile	Coming soon
AccuVac™ Smoke Evacuation Pencil Kits		
E2350HS**	Rocker switch pencil with EDGE™ coated blade, smoke evacuation attachment, and holster	25/case
E2450HS**	Button switch pencil with EDGE™ coated blade, smoke evacuation attachment, and holster	25/case
E2515HS**	Rocker switch pencil with smoke evacuation, attachment and holster	25/case
E2516HS**	Button switch pencil with smoke evacuation, attachment and holster	25/case
E3590	AccuVac™ smoke evacuation attachment	25/case
E3595	AccuVac™ smoke evacuation attachment extender	10/case

*In direct postsurgical surveys of surgeons and nurses on their use of the RapidVac™ Smoke Evacuator, the majority affirmed support for the following: (1) Easy to set up and easy to connect tubing (32 out of 32); (2) Filter easy to install (32 out of 32); (3) Filter easy to remove (31 out of 31); (4) Easy to adjust outflow (31 out of 31); (5) Quieter in the O.R. than expected (20 out of 20); (6) Improved visibility (31 out of 31). Data on file at Covidien.

*Requires SEA3710

**Requires SEA3710



COVIDIEN, COVIDIEN with logo and "positive results for life" are trademarks of Covidien AG. © 2009 Covidien. All rights reserved.

R0007519 Rev. 2009/04