

ADEMCO

K0017 4/16/02
No. 5815MN
Contact Transmitter

Preliminary Installation Instructions

Use the 5815MN shock sensor only with alarm systems that support 5800 series wireless devices. The transmitter has its own unique serial number permanently assigned during manufacture, which must be entered into the control panel prior to the transmitter's usage. Refer to the control unit's installation instruction for programming details.

Note: During programming of the control unit, 5815MN transmitters should be treated as "RF" (i.e. supervised RF) Type. The 5815MN is assigned as one zone.

Mounting

Before mounting the transmitter permanently, conduct Go/No Go tests (see control's instructions) to verify adequate signal strength from the mounting location.

- 1) Learn serial number as described in the control panel installation instructions. To cause the sensor to transmit, fault and restore the magnetic contact.
- 2) Determine mounting location.
- 3) Verify range by holding the sensor in the approximate mounting location and faulting the magnetic contact. The panel (in test mode) should respond to the transmissions. If not, find a more suitable mounting location.
- 4) Mount the transmitter and magnet with the appropriate mounting hardware.
- 5) Verify operation by faulting and restoring the magnetic contact – check for trip at alarm panel.

FCC Statement

FCC ID: CF88DL5815MN

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications

Contact Gap:

1/2 inch minimum

Unit Dimensions:

1.6" (40.64mm) x 1.6" (40.64mm) x 0.8" (20.32mm)

Battery:

Panasonic CR2, Sanyo CR2, and Duracell DLCR2.

Refer to the installation instructions for the receiver/control with which this device is used for warranty information, and details regarding the limitations of the entire alarm system.

ADEMCO **GROUP**

165 Eileen Way, Syosset NY 11791
Copyright© 2002 Pittway Corporation