


REV	DESCRIPTION	DATE
△		

300mm

90mm

Product instructions



U10ie  
Wireless headset

Welcome to use


Welcome to choose U10ie high quality wireless. This product is beautiful and elegant, with pure sound quality and distinct tones, which enables you to enjoy the beauty of hearing to the fullest. Please read the instructions carefully before using this product to ensure safety.

1. Reading instructions: please read all safety and operation instructions before using the product.
2. Reserve operating instructions: keep good operational instructions for future reference.
3. Comply with instructions: all operations and instructions should be followed.
4. Water content and moisture: in order to prevent fire and electric shock and other hazards, please do not put this product in rainy or humid environment.
5. Good warning: to prevent fire and electric shock and other hazards, please do not put this product in rainy or humid environment.
6. Storage location: Please place this product in a dry and stable position.
7. Cleaning: the products can only be polished with polished cloth or soft dry cloth. Never use furniture wax, benzene, insecticide or other volatile liquids to clean the product, otherwise it will corrode the product.
8. Foreign body intrusion: Please prevent foreign objects from falling into the product.
9. Maintenance: users should not try to do maintenance work. They should be dealt with by manufacturers or distributors.

Product features

1. Lighter, smaller, more free you don't feel in the ear. High hardness aluminum magnesium alloy, lightweight following design, truly lighter and firmer.
2. All-weather companionship. Built-in protection low energy consumption design, double battery life, all electronic listening to music for 10 hours, to meet daily music needs.
3. IPX5 moisture, right and soft, no longer extended. High strength, high elasticity, high toughness TPE, soft touch, not easy to wear.
4. Long to wear for long time. Listen to enjoy. Call to enjoy in ear, medical grade biological silicone ear mold, ergonomic design, flexible fitting different ear shape.
5. Design of magnetic absorption with wear and unloading. The rear end of the ear shell has a magnetic absorption function. When it is not used for earphones, it is adsorbed back to back and hung on the chest. With the unlock, free movement, friction and general.
6. Three key free control, simple manipulation. Through the touch of the ear shell, you can also use as a key for mobile phone, you can also use as a key for mobile phone.
7. Connection distance 10 meters. Choose professional chip, 4.1 version, the connection distance is 10 meters, and can connect with two devices at the same time. The signal is stable and the transmission is smooth.
8. More compatible, support IOS power display, unpaired. Compatible with most common Android and IOS mobile phones, compatible with streaming music, communication APP, read IOS power display, Android part support.

Product list




1. Headset
2. Instructions
3. Silicone ear cover three sets
4. Case line

Headset specifications

Name: Wireless headset  
Model: U10ie  
Color: Gray  
Driver unit: 9.0mm  
Frequency response: 20Hz-20KHz  
Impedance: 16Ω ± 20%  
Sensitivity: 84dB ± 3dB @1KHz  
Communication mode: VER.4.1  
Weight: about 18.8g  
Maximum communication distance: about 10m


How to use

1. Key and use




Volume - / Last    Volume + / Next

2. Charging




How to use

3. Pairing




1. Turn on or turn off the headset.
2. When the headset is turned on, if the first connection is made, the headset will automatically enter the pairing mode.
3. Connection device




Earphones

1. Select suitable earplug




2. On the back of the neck



3. Magnetic absorption function

When the headphones are not used, the two sides of the earphone can be magnetically adsorbed together. Easy to carry, avoid shading.



FCC Warning

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: Any changes or modifications to this unit not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

Thank you for the purchase of our products!

Environmental Protection Regulation KA-Q-Q-S-042( RoHS 2.0 )

<b>MATERIAL</b>						
<b>FINISH</b>						
SELECT V						✓
DIM TOL	1	2	3	4	EXTRA	
~8	0.03	0.05	0.10	0.20	0.5	
8~25	0.05	0.08	0.20	0.30	0.5	
25~80	0.08	0.12	0.30	0.40	2.0	
80~250	0.12	0.20	0.40	0.50	2.0	
250~	0.20	0.30	0.50	0.60	5.0	

**KINGSTATE** KINGSTATE ELECTRONICS CORP.

http://www.kingstate.com.tw

<b>DESCRIPTION</b>				
<b>PART NO.</b> KJ504SPPP03-A2		<b>DRAWN NO.</b> PKX-C304		
<b>THIRD ANGLE PROJECTION</b>		<b>SCALE</b> 1/1	<b>Unit:</b> mm	<b>SHFET</b> 1/1

7      6      5      4      3      2      1