










Company		Cadwell Laboratories Inc	CareFusion	CleveMed	Compumedics USA Inc
<b>Product</b>		 Easy III Amplifier with Easy III Software	 SomnoStar Software with z4 Amplifier	 Sapphire PSG	 Grael HD-PSG Amplifier with ProFusion PSG 3 Software
<b>Website</b>		www.cadwell.com	www.carefusion.com	www.clevedem.com	www.compumedics.com
PSG SOFTWARE	<b>Year Introduced</b>	2007	1986	2003	2007
	<b>Current Version Number</b>	4.0	11.1	7.9	3.4
	<b>Updates Policy</b>	Included	Included unless hardware/training required; included with service contract	Included during warranty period; discounted after	Updates within version included; upgrades to new version for special pricing, with further discounts for customers under warranty or service contract
	<b>Custom Reports</b>	Included	Included (customer may create own reports)	Included	Create your own via imbedded ProFusion Report tools in Microsoft Word
LAB MANAGEMENT SOFTWARE	<b>SQL Based</b>	No	Yes	No	Yes
	<b>Separate or Integrated with PSG</b>	Integrated	Integrated	Integrated	Integrated
	<b>Queryable Search Engine</b>	Yes (via clinical database report generator)	Yes	No	Yes
	<b>HL 7 Enabled</b>	Yes (optional)	Yes	No	Yes (optional)
AMPLIFIERS	<b>Year Introduced</b>	2007	2008	2007	2009
	<b>Number of Channels</b>	32-128	48	21	40 AC; 77 total
	<b>Number of Auxiliary Device Channels</b>	8DC; 12 EasyNet	16	1	16
	<b>Works With Devices That Offer +/-1 or +/-5 Volts</b>	Yes	Yes	+/- 1 V only	Yes
	<b>Sampling Rates (Hz)</b>	4,000	2,000	256	Up to 2,048 per channel; oximeter up to 256
	<b>AASM Compliant</b>	Yes	Yes	Yes	Yes
	<b>Transmission Mode</b>	Cat 5/6	Cat 5	Wireless	Cat 5e
	<b>Warranty (years)</b>	1	1 (extended available)	1	1
VIDEO	<b>Fixed Focus or PTZ</b>	Both available	Both	Compatible with both	Both
	<b>Integrated IFR Generator or Stand-alone</b>	Both available	Stand-alone	Integrated	Both available
	<b>Adjustable Frame Rate During Collection</b>	No	Yes	Yes	No
	<b>Post-acquisition Editing</b>	Yes	Yes	No	Yes
	<b>Integrated Intercom</b>	Yes (optional)	No	No	Yes (Louroe)
TRANSDUCERS	<b>RIP Belts (Reusable/ Disposable)</b>	Both available	Both	Both available	Both available
	<b>RIP Integrated to Amplifier or Requires Conditioner Box</b>	Conditioner box integrated in belts	Neither	Conditioner box	Integrated
	<b>Installation Included in Purchase</b>	Yes	Yes	Yes	Yes

Company		Natus Medical Inc	Nihon Kohden America Inc	Philips Respironics	Sleepvirtual	SOMNOmedics America Inc
Product		 Sandman	 PSG-1100 Sleep System	 Alice 6 LDxN with Sleepware G3	 BW3 PSG Plus	 SOMNOscreen plus PSG with DOMINO Software
Website		www.natus.com	us.nihonkohden.com	www.philips.com/sleepdx	www.sleepvirtual.com	www.somnomedics-diag-nostics.com
PSG SOFTWARE	Year Introduced	1995	1998	2011	2015	2007
	Current Version Number	10.1.3	9	3.8	1.95	2.8.0
	Updates Policy	Updates included; charge for upgrades	Updates included; charge for upgrades	Included	Included	Included
	Custom Reports	Additional fee	Customer may create own; will create for a fee	Customer may create their own or 4 hours of custom report writing with system purchase	Included	Customer may create own, company created templates
LAB MANAGEMENT SOFTWARE	SQL Based	Yes	Yes	Yes (via third party Lab Manager Solution)	Yes	Yes
	Separate or Integrated with PSG	Enterprise	Integrated	Separate	Integrated	Integrated
	Queryable Search Engine	Yes	Yes	Yes	Yes	Yes
	HL 7 Enabled	Yes	Yes	Yes (optional)	Yes	Yes
AMPLIFIERS	Year Introduced	2012 (latest iteration)	2013	2011	2012	2007
	Number of Channels	60 and 32	42	57	50	58
	Number of Auxiliary Device Channels	8 DC	6-14	8	8	16
	Works With Devices That Offer +/-1 or +/-5 Volts	Yes	Yes	Yes (+/- 1.65 V)	Yes	Yes
	Sampling Rates (Hz)	N7000: 2,000; S4500: 500	Up to 2,000	2,000	2,000	Up to 4,000
	AASM Compliant	Yes	Yes	Yes	Yes	Yes
	Transmission Mode	IEEE802.11G: IEEE802.11B, TCP/IP	IP addressable	Cat 5	TCP/IP	Wireless
	Warranty (years)	1	1	2	2	2
VIDEO	Fixed Focus or PTZ	Both	Both	Both available	Both	Both available
	Integrated IFR Generator or Stand-alone	Both	Both	Integrated on fixed focus; stand-alone on PTZ	Both	Integrated
	Adjustable Frame Rate During Collection	Yes	Yes	Yes	Yes	Yes
	Post-acquisition Editing	Yes	Yes	Yes	Yes	Yes
	Integrated Intercom	Yes	No	Yes (by VoIP)	Yes	Yes
TRANSDUCERS	RIP Belts (Reusable/ Disposable)	Both	Both available	Reusable zRIP DuraBelt	Both	Both
	RIP Integrated to Amplifier or Requires Conditioner Box	Integrated	Conditioner box	Integrated	Integrated	Conditioner box
	Installation Included in Purchase	Yes	No	Yes	Yes	Yes

Information for this guide based on data submitted by product manufacturers. Sleep Review strives for accuracy in all data but cannot be held responsible for claims made by manufacturers.