

### **Soft Touch Flexible Sharpening Wheel\***

| Stock#                  | Usage                   | Function                                                         |
|-------------------------|-------------------------|------------------------------------------------------------------|
| FS-300C<br>coarse wheel | 2,000 ~ 2,500<br>passes | For re-profiling or to repair<br>knives with chip(s) up to 1/8". |
| FS-302M<br>Medium wheel | 1,500 ~ 1,800<br>passes | For heavy commercial use or<br>speed sharpening.                 |
| FS-304F<br>Fine wheel   | 1,000 ~ 1,200<br>passes | To get razor sharp. Not for<br>Pre-sharpening (re-profiling).    |

**Sharpening wheel's life depends on:**

1. How many knives you will sharpen in a week
2. Condition of your knives
3. Level of sharpening skills

**Size of Wheel (L X W X H):** 5.5" x 3.0" x 2.8"