



## Reference Guide

#Color Chart																							
	Chroma Beige 90	Steel Grey 92	Silver Grey 91	Chestnut Brown 93	Silver 44	Terra Cotta 94	Black 63	Mother of Pearl 66	Pure White 98	Think Pink 79	Vivid Lilac 95	Pale Green 99	Cabernet Red 73	Midnight Blue 68	Sunset Orange 69	Emerald Green 48	Purple 45	Blue 47	Red 46	Baby Blue 42	Baby Pink 43		
Model																							
Opn 1 miniRITE																							
Alta2 Pro																							
Alta2 Pro designRITE																							
Sensei Pro																							

■ not available

### Custom Mold Styles

**LiteTip**  
(Hollow)



**MicroMold**  
(Solid)



**Power Receiver Mold**  
(Opn, Alta2 Pro, Sensei Pro)



**VarioTherm**



**MicroShell**  
(Opn)



### Retention Locks

All mold styles are offered with canal locks and skeleton locks for better retention. Helix locks, Half Skeleton and Semi Skeleton styles are also available upon request. (Retention Lock options vary by style and material selected.)

**Canal Lock**



**Helix Lock**  
(Available in hard material only)



**Skeleton Lock**



**Half Skeleton**



**Semi Skeleton**  
(Available in hard material only)



### \*VarioTherm Material

VarioTherm is a body temperature-reactive plastic for soft flexible earmolds. The unique properties of this material allow the mold to remain hard at room temperature for ease of insertion and then soften (become more flexible) at body temperature for increased comfort and optimum sealing.

**Please note: This material requires gentle warming/softening of the mold with a hair dryer before insertion or removal of the receiver.**

### Wax Protection System

Custom molds (except LiteTips) use the ProWax system. All miniFit receivers and the MicroShell use the ProWax miniFit wax system.

